



Monitor Size 17" Viewable Size 16"  
Dot Pitch 0.26mm  
Maximum Resolution and Refresh 1600 x 1200 @ 75Hz  
Horizontal Frequency 30 - 96Khz

710P

 **Hansol**

[www.hansol-uk.com](http://www.hansol-uk.com)

...it has to be.

## Hansol Europe Ltd

7-8 Ancells Court  
Rye Close  
Ancells Business Park  
Fleet, Hampshire  
GU13 8UY, U.K.

Tel:+44 (0)1252 360400

Fax:+44 (0)1252 360401

www.hansol-uk.com

Contact: sales@hansol-uk.com

Hansol Deutschland Tel:+49 6196 927570

Hansol Benelux Tel:+31 33 299 06 22

Hansol Nordic Tel: 040 661 60 70

# 710P



## SPECIFICATIONS

CRT	Size	17" Diagonal
	Dot Pitch	0.26mm
	Viewable Size	16"
	Display Area	326mm x 244mm
	Shadow Mask	INVAR
Resolution	Maximum	1600 x 1200 @ 75Hz
	Optimum	1280 x 1024 @ 85Hz
Bandwidth		157Mhz
Scanning Frequency	Horizontal	30 – 96Khz
	Vertical	47 – 160Hz
Microprocessor		Yes
Colour Temperature		Yes
Plug & Play		Yes
Mac Compatibility		Yes (May need adaptor)
Speaker		No
On-Screen Display		Yes
Universal Power		Yes
Input Connector		15-pin D-Sub
Power Management		VESA DPMS, NUTEK, EPA Energy Star
Standards	EMI	FCC-B, MPRII, CISPR22, VCCI, TCO99 (option)
	Safety Ergonomics	UL, CSA, TUV, CE ISO9241, GS
Weight	Product	15.7Kg
	Shipping	18.5Kg
Dimensions	Product W x H x D	418mm x 417mm x 419mm
	Shipping W x H x D	530mm x 462mm x 508mm

Hansol