



# RACK PDU, BASIC, 0U/1U, 220-240V, 32A, (4) C19, EMEA/ ASIA

AP6032A

#### **Overview**

Lead time Usually in Stock

#### Main

Colour	Black
Product or component type	PDU
PDU type	Basic
Cord length	3.7 m
Provided equipment	Installation guide Safety guide

## Complementary

Input Voltage	200 V	
_	230 V	
	240 V	
Height	4.4 cm	
Width	43.8 cm	
Output Voltage	200 V	
	230 V	
	240 V	
Depth	9.3 cm	
Net weight	2.78 kg	
Mounting location	Front	
	Rear	
Mounting preference	No preference	
Input Plug Type	IEC 60309 32 A 2P + E	
Mounting mode	Not rack-mountable	
Rack units	1U	
Mounting position	Horizontal	
Permissible voltage	200240 V	
Max line current	32 A	
Input current limits	32 A	
Load capacity	7400 VA	
Network frequency	50/60 Hz	
Outlet type and quantity	4 IEC 60320 C19	

## **Environment**

Product certifications	CE	
	IRAM	
	VDE	

## **Packing Units**

9	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	20.8 cm
Package 1 Width	18 cm
Package 1 Length	47.8 cm
Package 1 Weight	3.75 kg
SCC14	10731304327827

## **Contractual warranty**

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

### ☑ Environmental footprint

Environmental Disclosure

Product Environmental Profile

#### **Use Better**

<b>⊗</b> Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
SCIP Number	1cdb2fed-a06f-4574-913d-8df8e70936b2
REACh Regulation	REACh Declaration
Optimized Energy Efficiency	Energy efficient product

#### **Use Again**

○ Repack and remanufacture		
Circularity Profile	End of Life Information	
Take-back	Yes	