

### FR28 - Bizflame Work FR Coverall

**Collection:** Bizflame™ Work

**Range:** Flame Resistant Multi-Norm

**Shell Fabric:** Bizflame Work: 99% Cotton, 1% Carbon Fibre, 280g

**Outer Carton:** 12



### Product information

Constructed using a lighter weight highly innovative flame resistant BizFlame Work fabric.

#### Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards.

#### Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

### Standards

EN ISO 11612 (A1+A2, B1, C1, F1)  
EN ISO 11611 Class 2 (A1+A2)  
EN 1149 -5  
EN 17353 Type B2

### Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Action back for extra freedom of movement
- Hook and loop cuffs for a secure fit
- Two tier knee pad pockets allowing two positioning options
- Side access openings
- Sleeve pocket
- Sew on flame resistant industrial wash tape
- Two-way zip for quick and easy access

### FR28 - Bizflame Work FR Coverall Commodity Code: 6211321000

#### Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)  
Bracetown Business Park  
D15 YN2P, Ireland  
Cert No: 2777/13017-03/E00-00

#### Wash Care



#### Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
FR28RERS	Red	43.0	28.0	46.0	1.3300	0.0554	5036108213290	15036108698971
FR28RERM	Red	43.0	28.0	46.0	1.3700	0.0554	5036108213283	15036108698964
FR28RERL	Red	43.0	28.0	46.0	1.4200	0.0554	5036108213276	15036108698957
FR28RERXL	Red	43.0	28.0	46.0	1.4800	0.0554	5036108213306	15036108698988
FR28RERXXL	Red	43.0	28.0	46.0	1.5100	0.0554	5036108213313	15036108698995
FR28RERXXXL	Red	43.0	28.0	46.0	1.6200	0.0554	5036108213320	15036108699008