



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #3-1376430-5
025/040 135P CAP HSG ASSY



TE Part #5-1744107-5
EP HDR ASSY 7P omit 2&4&6,black



TE Part #2-1554809-3
RITS CONN. PLUG ASSY 3P BLUE COVER



TE Part #7-1744103-2
EP HDR ASSY 2P,Gray



TE Part #1-1744109-6
EP HDR ASSY 11P omit 2&4&6&8&10,
natural

TE Part #3-1971032-4
4POS HEADER ASSEMBLY FOR GIC
2.0 EV

TE Part #1-5174912-2
040 MLC MK2 36POS CAP ASSY H AU

TE Part #1-1744106-7
EP HDR ASSY 6P,natural

TE Part #7-1744103-1
EP HDR ASSY 3P omit 2, Gray

TE Part #1-5175976-2
040 MLC MK2 28POS CAP ASSY H AU

Documents

Product Drawings

1.25FP,R08,SL,B,N,TR

English

CAD Files

Customer View Model

ENG_CVM_CVM_3-175636-8_D.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-175636-8_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-175636-8_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

AMP 1.25mm F-P Connector (Board To Board)

Japanese

Product Specification

Japanese