



**1200**  
LUMEN



**2-200H**  
RUNTIME



**251M**  
RANGE



**IP68/IK07**  
IP RATING

## NEW WCFL12 - WIRELESS CHARGING FLASHLIGHT

- Super bright 1200 lumen white LED, 6500K
- Ultra tough nylon, aluminium & TPR construction
- Multi-faceted reflector for long distance beam
- Dual switches for easy mode selection
- Memory switch - remembers last mode used
- Press & hold for 2 seconds for Strobe mode
- IP68 dust & water proof - 1m submersible
- IK07 super tough shock construction - 2m drop resistant
- High quality 3.7v 2600mAh li-ion battery
- Built-in USB-C charging port with protective cover
- 3 Battery level and charging indicator lights
- Can be wireless charged with Unilite WCSGL or WCDL wireless charging pads
- 2A direct USB-C charging - fast 4 hours charge time
- 1m USB-C charging cable included

**BATTERY** 3.7v 2600mAh Li-ion Rechargeable Battery  
**WEIGHT** 215g  
**DIMENSION** Ø41 x 159mm



BATTERY & CHARGING INDICATORS



USB-C DIRECT CHARGING PORT



**USB**  
TYPE-C

