

Datasheet

RS Pro SafetySure 13A, BS Standard fixing, Passive, 2 Gang RCD Socket, Urea Formaldehyde, Flush Mount, Switched

RS Stock No: **687-7339**



Product Details

RS Pro 2-gang passive RCD socket in white colour, is made from urea formaldehyde for long life durability. It operates on a voltage rating of 230 V ac and current rating of 13 A. This flush mountable unit provides protection against the risk of electrocution and fire hazards. It has a dual earth terminals and is mechanically latched, no need to reset after power loss. The RCD socket meets BS7288: 1990 and BS1363 standards.

Features and Benefits

- Current rating 13 A
- Voltage rating 230 V ac
- Trip current of 30 mA
- Trip time of 30 ms
- Conforms to BS7288: 1990 and BS1363

Specifications:

Colour Family	White
Colour Shade	White
Colour	White
Current Rating	13 A
Dimensions (L x W x D)	147 x 86.5 x 35 mm
Earth Terminal	Yes
Faceplate Depth	16 mm
Faceplate Fixing	Screwed
Faceplate Mounting Type	Screwed
Finish	Polished
Fixing Standard	BS Standard
Height	86.5 mm
Material	Urea Formaldehyde
Minimum Box Depth	35 mm
Mounting Style	Flush Mount
Number of Gangs	2
Number of Poles	2
RCD Type	Passive
Socket Type	BS 1363, BS 7288
Switch Style	N/A
Switch Type	N/A
Switched	Yes
Trip Current	30 mA
Trip Speed	30 ms
Voltage Rating	230 V ac
Voltage Rating	230 V ac
Width	147 mm