

Datasheet

## RS Pro 80W Polycrystalline Flexible solar panel

RS Stock No: **914-8460**



### Product Details

RS Pro solar panel is well suited for use where a super robust, low profile and lightweight panel is needed or the substrate to which the panel will be fixed has a slight curve. The panel is ideal for marine buoys, boat decks and camper vans etc. This PV logic flexible solar panel with polycrystalline construction, has a power rating of 80 W.

### Features and Benefits

- Self-healing top surface
- Completely waterproof
- Cells protected from hot spots
- Superior design: No square edges
- Easy fix

**Specifications:**

Depth	3 mm
Dimensions	885 x 665 x 3 mm
Length	885 mm
Maximum Temperature	+80°C
Minimum Temperature	-40°C
Mounting Style	Wall Mount
Open Circuit Voltage	21.6 V
Power Rating	80 W
Protection Type	Hot Spot
Terminal Contact Type	Ring
Type	Polycrystalline
Width	665 mm