

A-10 ; 0...40 bar gauge; 4...20 mA, 2-W @ 8...30 V DC

Pressure transmitter Model A-10

Item number: 46879242

Quantity: 1 pcs.

Order code: A-10-6-BG440-HD1Z-AA-CGZ-ZW W1011A10Z-SZ3S-ZZFWPA-2AZZZSAZZZA3Z

Overview: A-10 ; 0...40 bar gauge; 4...20 mA, 2-W @ 8...30 V DC
Pressure transmitter Model A-10
Non-linearity: 0.5% BFSL
Process connection: G 1/4 A DIN EN ISO 1179-2; Sealing: NBR
Electrical connection: valve connector, size C
Pin assignment: U+=1, U-=2
Permissible medium temperature: 0...+80 °C
Approvals: cULus
Type of packaging: folding box single
WIKA standard - specification according to data sheet PE 81.60

Details: Pressure transmitter Model A-10
for general applications
Specifications according to data sheet: PE 81.60
Wetted parts: 316L
Case: 316L
Non-linearity: 0.5% BFSL
Unit: bar
Pressure type: gauge
Measuring range: 0...40 bar gauge
Process connection: G 1/4 A DIN EN ISO 1179-2
Sealing: NBR
Permissible medium temperature: 0...+80 °C
Output signal: 4 ... 20 mA, 2-wire
Power supply: 8...30 V DC
Electrical connection: valve connector, size C
Approvals: cULus
W1 (Wika standard)
Customer address: www.wika.com
Model name customer-specific: A-10
Pressure port: Standard
Type of packaging: folding box single
Sealing colour: WIKA standard (blue)
Test protocol: with test protocol
Main Language: English
Pin assignment: U+=1, U-=2
Customer-specific: WIKA standard - specification according to data sheet
Model: A-10 2.0

Date: 22/01/2024



Operating Instructions: with printed OI
Additional Data: without