

booted head for pushbutton XAC-B - white - 4 mm, -40..+70 °C

XACB9121

EAN Code: 3389110644586

Main

Range of product	Harmony XAC	
Product or component type	Head for push-button	
Component name	XACB	
Marking	Unmarked	
Operator additional information	Booted	
Operating travel	4 mm	
Cap/operator or lens colour	White	
Product compatibility	XENB XESD2251 XESD2241 XEND XESB2011 XENC XESD2201	
Sale per indivisible quantity	10	

Complementary

0.005 kg

Environment

Net weight

Standards	IEC 60947-5-1 CSA C22.2 No 14 IEC 60947-5-1	
Ambient air temperature for operation	-4070 °C	
Ambient air temperature for storage	-4070 °C	
Vibration resistance	15 gn (f= 10500 Hz) conforming to IEC 60068-2-6	
Shock resistance	100 gn conforming to IEC 60068-2-27	
Electrical shock protection class	Class II conforming to IEC 61140	
IP degree of protection	IP65 conforming to IEC 60529	
IK degree of protection	IK08 conforming to IEC 62262	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	2.7 cm

Package 1 Length	10.0 cm
Package 1 Weight	6.0 g
Unit Type of Package 2	BAG
Number of Units in Package 2	10
Package 2 Height	11.5 cm
Package 2 Width	2.7 cm
Package 2 Length	10.0 cm
Package 2 Weight	61.0 g

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Packaging made with recycled cardboard	No	
Packaging without single use plastic	No	
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
REACh Regulation	REACh Declaration	

Use Again

○ Repack and remanufacture		
Take-back	No	