
BACKSHELL KIT INCLUDES:


- (2) BACKSHELL HALVES
- (2) 4-40 THUMBSCREWS
- (2) HOUSING SCREWS & (2) NUTS
- (1) SET OF COMPRESSION INSERTS VARIOUS SIZES

DIAMETERS: 4mm (.157"), 5mm (.197"), 7mm (.276"), 9mm (.351")

NOTE: 9 POSITION HAS ONLY 1 THUMBSCREW

(OPPOSITE CABLE ENTRY)





DIMENSIONS (mm/in)						
SIZE:	A ±1.27	B ±.005	C ±.25	D ±.25		
9	31.00	24.99	36.30	15.00		
	1.220	0.984	1.429	0.591		
15	39.50	33.32	40.30	15.00		
	1.555	1.312	1.587	0.591		
25	53.20	47.04	40.30	15.00		
	2.094	1.852	1.587	0.591		
37	69.70	63.50	1.587	15.00		
	2.744	2.500	1.646	0.591		

ORDERING INFORMATION

SIZE:	P/N KITTED:	PRODUCT CODE:
9-WAY	6560-0107-11	MHD45PPK-9-BK-K
15-WAY	6560-0107-12	MHD45PPK-15-BK-K
25-WAY	6560-0107-13	MHD45PPK-25-BK-K
37-WAY	6560-0107-14	MHD45PPK-37-BK-K

SIZE:	P/N BULK:	PRODUCT CODE:
9-WAY	6561-0107-11	MHD45PPK-9-BK
15-WAY	6561-0107-12	MHD45PPK-15-BK
25-WAY	6561-0107-13	MHD45PPK-25-BK
37-WAY	6561-0107-14	MHD45PPK-37-BK

PLASTIC: ABS POLYLAC - BLACK - UL RECOGNIZED

4-40 THUMBSCREWS: STEEL - BLACK OXIDE HOOD SCREWS: STEEL - BLACK OXIDE

COMPRESSION INSERTS: ABS UL RECOGNIZED

NUTS: STEEL - STEEL - BLACK OXIDE

OPERATING TEMP: -55°C TO +110°C

CONNECTORS

MH CONNECTORS LTD.

THESE DRAWINGS AND SPECIFICATIONS ARE THE

WRITTEN PERMISSION.

PROPERTY OF MH CONNECTORS LTD. AND SHALL NOT

BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT

RAWN	DATE		
P. JENKIN	2	03-1	4-12
PPROVED	DATE		
D. CROFT		03-1	.4-12
CALE	SHEET	OF	RFV·

В

SCALE SHEET OF 1 1

DRAWING No

MHD45PPK SERIES

ROHS COMPLIANT