

Datasheet

RS Pro Plain Stainless Steel Pan Head Machine Screws, M3 x 16mm

RS Stock No: **526-978**



Product Details

RS Pro machine screw measuring M3 x 16 mm, is made of A2 grade plain stainless steel material. This pan head screw is fully threaded and it can be used in pre-tapped holes or can be used with conforming nuts and washers in through holes. The slotted drive screw is designed to give you ease of assembly. It is suitable for use in medical, food, domestic and construction applications. This machine screw meets DIN 85 standards.

Features and Benefits

- Good corrosion resistance
- Recyclable
- Non-magnetic
- Can be used up to 800°C

Specifications:

Drive Type	Slot
Finish	Plain
Head Shape	Pan
Material	Stainless Steel
Length	16 mm
Stainless Steel Type	304 (A2)
Thread Pitch	0.5
Thread Size (Metric)	M3
Head Diameter	3.6 to 5.3 mm
Head Height	1.66 to 1.8 mm
Slot Depth	0.7 mm
Slot Width	0.8 mm
Specification	DIN 85