

IN 19 L 10-140

Screwdriver bit socket 1/2"

Code	ETIM
6158110	EC002157
EAN	UNSPSC
4010886615812	27-11-17-01
Country of origin	eCl@ss
Germany	21-04-04-02
Customs tariff number	
82079030	



Article description

- Acc. to DIN 7422
- Square drive as per DIN 3120 - C 12,5, ISO 1174, with ball retention groove
- Manually operated, with non-slip cross knurling
- Chromed
- With pressed-in pin in GEDORE vanadium special steel, manganese-phosphated

Article information

Contents (Qty of pieces)	1	Drive connector square female [inch]	1/2"
Net weight [kg]	0,154 kg	Standard	DIN 7422 DIN 3120 - C 12,5 ISO 1174
Total length [mm]	140 mm	Width across flats l [mm]	10
Total width [mm]	22,5 mm	Backup	Ball Catching Cricket
Surface	chrome-plated	Tip length	102,0 mm
Material	Chrome-vanadium steel	Insert Ø Actuator	22,5 mm
Drive connector square female (metric)	12,5 mm		