



Product data sheet

Power tools for trade & industry

Polisher

PRO GPX 12V-77



Precision polishing with cordless freedom

The most important data

No-load speed	1,400 – 7,000 rpm
Polishing sponge, diameter	77 mm
Orbit diameter	12 mm

Part Number 0 601 9L4 000

Technical data

Technical data

No-load speed	1,400 – 7,000 rpm
Polishing sponge, diameter	77 mm
Packaging dimensions (width x length x height)	77 x 214 x 126 mm
Battery voltage, works with	12.0 V
Orbital stroke rate, up to	14,000 opm
Orbital stroke rate, from	2,800 opm
Orbit diameter	12 mm

Noise/vibration information

Polishing

Vibration emission value ah	3.2 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Consistent performance thanks to brushless motor
- Convenient and precise with variable speed trigger for fine adjustment
- Better control thanks to HMI with battery charge indicator and 5-level speed selection
- Comfortable to use with a lock-on switch for fatigue-free continuous operation
- Compact and ergonomic design makes removing holograms and light scratches in small spots easy

**HEAVY
DUTY**

Ø 77 mm

1400–
7000
min⁻¹/rpm

Ø 12 mm

SPEED
SELECTIONCONSTANT
SPEEDUSER
INTERFACE

ERGONOMIC

BRUSHLESS
MOTORL-BOXX
READY

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

