



■ TG40 to TG48

➔ Siliconized leather gloves

▶ STANDARD :

EN 420

EN 388

Mechanical protection: Abrasion: 2 - Slicing: 1 -

Tear: 2 - Perforation: 2



▶ USE :

The gloves assure a mechanical protection of Latex gloves (protection of the forearm).

▶ TECHNICAL SPECIFICATIONS :

5 fingers glove, siliconized natural cowhide full grain leather, American cut, webbed thumb, tightening grip at wrist with self-gripping ribbon, split leather cuff 100 mm.

Sewn with polyester/cotton thread.

Innocuousness, comfort and manual skill level 5.

Overall length of a glove: 305 mm.

Ref.	Size	Dimensions	Weight
TG47 08	8	approx. 305 x 135 x 20 mm	approx. 225 g
TG40 09	9	approx. 305 x 135 x 20 mm	approx. 225 g
TG45 10	10	approx. 305 x 135 x 20 mm	approx. 225 g
TG48 11	11	approx. 305 x 135 x 20 mm	approx. 225 g

Document not contractually binding, errors and omissions excepted.