

## Features

- Multi-language support
- Free Type and Windows Font support
- Defining user image library
- Simulation feature
- C/C++ real-time programming
- MQTT communications protocol
- SQL client property
- 16M Display Colour
- 1024x600 Display resolution

## RS PRO 10" Lite HMI Panel

RS Stock No.: 0315666



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

VNC remote control feature,  
SMB file sharing,  
Video playback feature,  
1x RS-232 + 1x RS485 + 1x USB host + 1x USB device  
BACNET MSTP,  
MODBUS-RTU / -ASCII (Master / Slave) communication,  
Compatible with OMRON Host Link, DELTA DVP Series PLCs.

## General Specifications

CPU	ARM Cortex-A Series
Flash Memory	8GB eMMC
RAM	512 MB DDR3 SDRAM
Backlight Life	50000 hours
Luminance (Cd/m2)	270

## Mechanical Specifications

Device Dimensions	278x200x50mm
Panel Cut-Out	265x186mm
Weight	1300gr

## Electrical Specifications

Operation Voltage	18...30Vdc
Power Consumption	8W (10.1")
RTD Battery / Life	CR2023 Button Cell Lithium bat. / 3V - 5 years

## Protection Category

Protection Class	IP65
------------------	------

## Approvals

Compliance/Certifications	CE Certificate
---------------------------	----------------

## Electrical Connection

