

# Neodymium Deep Pot Magnets (Internal Thread)



- 80°C Max operating temperature
- N35 Grade
- Galvanised
- Steel case which provides extra strong magnetism on one face only
- Ideal for magnetic holding, lifting, antenna mounting and positioning
- Neodymium iron boron rare earth material



RS PART NO	ECLIPSE PART NO	PULL FORCE (kg)	Dia (mm)	Height (mm)	Weight (g)	DESCRIPTION
9175614	E740NEO	0.6	6	20	4	6mm Neo deep pot magnet, internal
9175617	E741NEO	1.2	8	20	7.5	8mm Neo deep pot magnet, internal thread
9175611	E742NEO	2.4	10	20	11	10mm Neo deep pot magnet, internal thread
9175620	E743NEO	6.0	13	20	20	13mm Neo deep pot magnet, internal thread
9175623	E744NEO	9.0	16	20	30	16mm Neo deep pot magnet, internal thread
9175627	E745NEO	13.5	20	25	58	20mm Neo deep pot magnet, internal thread
9175636	E746NEO	19.0	25	35	131	25mm Neo deep pot magnet, internal thread
9175639	E747NEO	34.0	32	40	243	32mm Neo deep pot magnet, internal thread

All sizes and colours available from stock. Please get in touch for further information.

Eclipse Magnetics, Atlas Way, Sheffield, S4 7QQ, England  
T +44(0)114 225 0613 info@eclipsemagnetics.com  
F +44(0)114 225 0610 www.eclipsemagnetics.com



A world leader in magnetic technology

