

FEATURES

- Patented quick change die system for easy installation and removal
- No tools required for die changes
- Left and right handed operation
- Moulded plastic storage case for secure transport and storage

RS PRO Plier Crimping Tool, 0.1mm² to 10mm²

RS Stock No.: 828-0232



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO brand this quick release ratchet action crimping tool is designed to crimp various kinds of terminals onto appropriate wires and cables. With replaceable die sets designed to handle different set sizes of terminals, the crimping tool is ideal for production work and maintenance applications alike. The different crimp sizes are even colour-coded for further ease of use.

General Specifications

Crimp Tool Type	Plier
Crimp Connector Type	Insulated Terminals
Adjustable Ratchet	Yes
Applications	This versatile and reliable terminal crimper can be used to crimp all kinds of insulated terminals onto wires, and as such has a wide range of uses in electrical applications. These RS PRO ratcheting terminal crimpers can be used in: Prototyping, Electronics, Engineering, Test and Measurement

Mechanical Specifications

Overall Length	254mm
-----------------------	-------

Approvals

Standards Met	RoHS Compliant
----------------------	----------------



CONNECTOR TYPE	APPLICATION	QTY	MATERIAL
1 Die For Insulated Terminal	AWG 22-18/16-14/12-10 DIN 0.5-1.0/1.5-2.5/4-6 mm ²	1 Set	AISI-4140 Treatment: Finished with heat treatment Surface Treatment: Zinc phosphate
2 Die For Non-Insulated Terminal	AWG 20-16/16-14/12-10/8 DIN 0.5-1.5 / 1.5-2.5 / 4-6 / 10 mm ²	1 Set	
3 Die For Open Barrel Terminal	AWG 20-18/16-14/12-10 DIN 0.5-1.0/1.5-2.5/4-6 mm ²	1 Set	
4 Die For Open Barrel Terminal	AWG 26-24/24-22/22-18 DIN 0.1-0.25/0.25-0.5/0.5-1.0 mm ²	1 Set	
5 Die For Open Barrel Terminal & D-Sub, V3.5	AWG 14 / 22 / 8-6 DIN 2.5 / 0.5 / 8-10 mm ²	1 Set	
6 Die For Spark Plug Connector	AWG 17 1mm ²	1 Set	
7 10" Quick Change Ratchet Crimper		1 Pc	Carbon Steel (body)

