

IP65 LED surface mounted non-corrosive fitting



LED open single



LED open twin



PRODUCT CODE	DESCRIPTION
795-9785	1 x 24W LED Non-corrosive fitting
795-9788	2 x 24W LED Non-corrosive fitting
795-9782	1 x 40W LED Non-corrosive fitting
795-9791	2 x 40W LED Non-corrosive fitting

APPLICATIONS

- Industrial areas
- Garages and workshops

SPECIFICATION


- IP65 rated
- Upto 40% Energy saving
- Available in 1x24W or 2x24W LED (4ft body), 1x40W or 2x40W (5ft body)
- Colour Temperature 5500K
- CRI. 70
- Lumen output: 1x24W - 2660, 2x24W - 4800, 1x40W - 3860, 2x40W - 7530
- Complete with LED driver - LED life 30,000 hrs (average)

CONSTRUCTION

- ABS base
- Polycarbonate controller
- Stainless steel clips
- Supplied complete with suspension eyes and stainless steel mounting brackets

OPTIONS

- Emergency available (Maintained 3 hours)
- DALI dimming available
- Sensor. Please enquire before specifying or ordering



	LENGTHmm	WIDTHmm	HEIGHTmm	CLIPS
1x24W	1270	93	100	10
2x24W	1270	140	100	10
1x40W	1565	93	100	12
2x40W	1565	140	100	12