

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought





TE Part #2-5747708-0  
25 RCPT SP/FMS BRDLK



TE Part #CAT-025-DPAVS2274  
D-Sub Plug Assembly: Standard, Vertical, Shell Size 2, 2.74mm



TE Part #640452-2  
02P MTA100 HDR ASSY SQ STR




TE Part #1-6609104-5  
PE0SXSSX0=C1162




TE Part #2301840-1  
AMPL REC HD20, VERT, 15P, B/L,4-40 S/LOC



TE Part #87922-4  
16 MODIV HSG W/STR RLF DR MRKD



TE Part #6-87756-8  
MOD IV RECP LP



TE Part #208945-5  
SZ 14 UNASSM KIT,CMC



TE Part #5-103635-1  
02 MTE HDR SRRA LTCH.100CL LF

Documents

Product Drawings

T81H5D312-05

English

T81H5D312-05

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_5-1393779-5\_C3.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_5-1393779-5\_C3.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_5-1393779-5\_C3.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



---

Datasheets & Catalog Pages

T81N/T81H Ultraminiature, High Density PC Board Relay

English

---

Product Specifications

Definitions General Purpose Relays

English