


Technical data sheet

Article number:**170-01107****Twist-In-FR 32**

Product Group	Self-closing, flame-retardant polyester sleeving
Product Family	Helagaine Twist-In-FR
Material	Polyester (PET)
Colour	Black with White Identification Yarn (BKIDWH)

Application Method	For optimum cable protection including flexibility, we recommend that a filling level of 75% is not exceeded.
Application Range	Indoor Use
Bundle Ø max.	32 mm
Bundle Ø min.	29 mm
Melting Point	+240 °C
Operating Temperature	-50 °C to +125 °C
Package Content	15 m
Package Content packed in	reel
Specifications	ECE R-118-03 Abschnitt 8 / Annex 8, EN 45545-2
UL-File Number	E197993

HF ✓ **RoHS** ✓**EN 45545-2****ECE R-118**