

Professionally approved products.

Datasheet

20 mm Hydraulic Circular Punch & Die Combinations



Description

A complete easy to use System enabling a wide variety of hole configurations to be punched by hand. Suitable for sheet steel, stainless, non-ferrous metals and plastics. Ideal for switchgear manufacturers, electricians, plumbers and handcrafters. Heat treated steel punches and dies manufactured to close tolerances will punch burr free holes up to 2mm thick in steel and 3mm thick in aluminium.



Professionally approved products.

Size	Pilot hole	Bolt size	Manuform Part	Thrust Bearing
Metric Round Sizes				
12.5	10	8	970-0010	NA
14.5	10	8	970-0020	NA
16.5	10	8	970-0030	NA
18	12	10	970-0040	NA
20	12	10	970-0050	NA
22.5	12	10	970-0060	NA
25	12	10	970-0070	NA
27.5	12	10	970-0080	NA
30	12	10	970-0090	YES
32	14.5	12		YES
35	14.5	12	970-0100	YES
40	14.5	12	970-0110	YES
45	20	16	970-0120	YES
50	20	16	970-0130	YES
60	20	16	970-0140	YES
70	20	16	970-0150	YES
75	20	16	970-0160	YES
76.2	20	16		YES

RS Stock No. [543-579](#)

RS Stock No. [543-585](#)