

FLEXLAB, bezel, transparent, transparent



fields of application

- Measurement-control-regulation
- Electrical engineering
- Mechanical and system engineering
- Vehicle construction
- Handheld terminals
- Industrial robots

description

technical data

➤ general

Bezel color	transparent
Property of bezel / mushroom	transparent
Operating temperature, min.	-25 °C
Operating temperature, max.	70 °C
Storage temperature, min.	-40 °C
Storage temperature, max.	80 °C
illuminated	Yes
Packaging unit	10 pcs.
net weight	0.1 g
MOQ order	10 pcs.
RoHS compliant	Yes
REACH compliant	Yes
Component material	Plastic

➤ mounting diameters

Outside dimension, length	22.15 mm
Outside dimension, width	22.15 mm
Outside dimension, height	2.85 mm

➤ mechanical data

Fixing	Latching
--------	----------

direct links

- [RAFI eCatalog](#)