



Part Number : [1200698601](#)

Product Description : Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 8 Poles, A-Coded, Female (Straight) to Pigtail, 24 AWG, Shielded Black WSOR Cable, 5.0m (16.40') Length

Series Number : 120069

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : 808S00BS2M050



Documents & Resources

Drawings

[1200698601_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120069
Description	Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 8 Poles, A-Coded, Female (Straight) to Pigtail, 24 AWG, Shielded Black WSOR Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	889056131223

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	30V

Physical

Cable Diameter	6.90mm (.272")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black

Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Knurled Hexnut, Threaded
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	369.000/g
Orientation	Straight to Pigtail
Poles	8
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215, Shielded TPU
Wire Size (AWG)	24