



K3MA-L-C 24VAC/DC

Temperature meter, DIN 96x48 mm, color change display, thermocouple/ RTD input, 1C/O relay output, 24 VAC/DC

Specifications

Type	Temperature
Input range	-200° to 1800° C
Size	1/8 DIN (96 x 48 mm)
Number of digits	4
Output type	Relay
Contact description	SPDT
Supply voltage AC	20.4-26.4 V
Supply voltage DC	20.4-26.4 V
Accuracy	+/- 0.1% full scale
Sample rate	500 ms
Communication port(s)	None
Features	Colour change display
Product Width (unpacked)	96 mm
Product Height (unpacked)	48 mm
Product Depth (unpacked)	80 mm
Temperature input type	B, E, J, JPt100, K, L, N, Pt100, R, S, T, U

Accessories



K32-49HC

Hard cover for use with 96x48mm panel meter



K32-49SC

Splash-proof soft cover for use with 96x48mm panel meter

CAD Library



Colour Change Displays Leaflet

EN PDF 272 KB



K3MA Series Digital Panel Meters Users Manual

EN PDF 7.29 MB



K3MA series Brochure

EN PDF 362 KB



K3MA series Leaflet

EN PDF 540 KB



K3MA-L Temperature Meter Datasheet

EN PDF 458 KB