



Product data sheet

Power tools for trade & industry

Cordless Impact Driver/Wrench

PRO GDS 18V-780



Compact and powerful: the easy way to tackle tough work

The most important data

Battery voltage	18.0 V
Torque, max.	780 Nm

Part Number 0 601 9P4 000

Technical data

Technical data

Weight excl. battery	2.1 kg
Torque, max.	780 Nm
Impact rate	1,900-2,400 bpm
Impact rate (2nd level)	2,100 bpm
Impact rate (3rd level)	2,400 bpm
Battery voltage	18.0 V
Breakaway torque, max.	1,000 Nm
Packaging dimensions (width x length x height)	198 x 249 x 103 mm
BITURBO	No

Noise/vibration information

Tightening screws and nuts of maximum permitted size

Vibration emission value ah	14.9 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Tackles tough bolting work with ease thanks to high tightening torque of 780 Nm and untightening torque of 1000 Nm
- Compact design with short 170 mm head length is ideal for working in narrow spaces
- Durable and robust with ½" tool holder and an extra protection ring that reduces stress by 20%
- Handles many applications thanks to multiple operating modes



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

