

Datasheet

RS Pro Straight 50Ω Panel Mount Bulkhead Fitting BNC Connector, jack, Solder Termination Nickel

RS Stock No: **546-4910**



Product Details

RS Pro straight panel mount bulkhead fitting BNC connector has a nickel plated brass and ABS body, nut, washer and gold plated centre contact. This panel mount female connector features 50 Ω impedance. It is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Nickel plated brass and ABS body, nut, washer and gold plated centre contact
- Solder termination method
- Female connector
- Suitable for a variety of applications including video signalling and test equipment

**Specifications:**

Body Orientation	Straight
Body Plating	Nickel
Bulkhead	Yes
Contact Material	Brass
Contact Plating	Gold
Gender	Female
Impedance	50 Ω
Mounting Type	Panel Mount
Operating Frequency	4 GHz
Polarity	Normal
Termination Method	Solder
Operating Temperature Range	-40 to +60°C
Standards Met	RoHS Compliant
Voltage Rating	500 V (Working)