

Features

- The special 60° angle makes the tool ideal for hard-to-reach areas.
- For copper wire Ø 1.02mm (18 awg)
- Steel thickness 3mm.
- ESD-safe
- Anti-reflection phosphating surface treatment
- Anti-slip bi-material dolphin handle with light and comfortable grip
- Made in Italy

RS PRO ESD Safe Flush End Cutters, Medium

RS Stock No.: 0616310



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO ESD Safe Flush End Cutters

RS PRO cutter has flush end cutter for clean cuts. The special 60° angle makes the tool ideal for hard-to-reach areas.

For copper wire Ø 1.02mm (18 awg) Steel thickness 3mm. Tool is equipped with a return spring designed to have a constant force, thus reducing operator effort.

ESD-safe version. Made with high carbon steel and undergo a controlled atmosphere heat treatment. The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.

The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator.

General Specifications

Cutter Type	Oblique Cutters
Materials Cut	Copper Wire Ø 1.02mm (18 awg)
No Sparking	No
Overall Length	152mm +/- 2mm
VDE/1000V Approved	No
Height Safe	No
ESD Safe	Yes
Material	High Carbon Steel
Maximum Cutting Capacity	1.02mm
Cut Type	Flush

Approvals

Declarations	REACH DoC
Standards Met	IEC 61340-5-1 (ESD)

