


# MARQUARDT

## SERIES 1800 - SINGLE AND DOUBLE-POLE ROCKER SWITCHES

TO 12 (4) A 250 V AC

 double-pole		ON/OFF switch (DPST)															
		1805.6102	1805.6108	1805.7104	1805.7109	1805.7110	1805.7112	1805.7118	1802.1120	1802.1121	1802.1123	1802.1136	1802.2112	1802.2504	1802.3311	1802.6123	1802.1101
Voltage lamp in V		230	230	230	230	230	110 -230	110 -230									
Actuator color / printing																	
Housing color		black								black							
12 (4) A 250 V AC 1E4							●	●	●	●	●	●	●	●	●	●	●
10 (4) A 250 V AC 1E4		●	●	●	●	●											●
8 (8) A 250 V AC 5E4							●	●	●	●	●	●	●	●	●	●	
6 (4) A 250 V AC 5E4		●	●	●	●	●											●
6 (2) A 250 V AC 1E4																	
4 (3) A 250 V AC 6E3																	
4 (2) A 250 V AC 1E4																	
30 mA 12 V 5E4																	
30 mA 12 V DC 5E4																	
15 A 250 V AC 1 1/2 HP							●	●	●	●	●	●	●	●	●	●	
15 A 125 V AC 3/4 HP							●	●	●	●	●	●	●	●	●	●	
10 A 250 V AC 1/2 HP																	
10 A 125 V AC 1/3 HP																	
6 A 250 V AC 1/2 HP		●	●	●	●	●											●
6 A 125 V AC 1/4 HP																	●
6 A 125 - 250 V AC 1/8 HP																	
6 A 125 V AC 1/10 HP																	
4 A 250 V AC 1/10 HP																	
Connection type																	
Connection description				4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.8	4.3 long	4.8 75° angled MG		4.8
Inrush current in A (capacitive)		50	50	50	50	50	70	70	70	70	70	70	70	70	70	70	50
Contact distance in mm		≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3	≥3
Contact material		Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag	Ag
EN 60335 cap. 30 conform *G*							●										
Miscellaneous		Installation depth 17.5	Installation depth 17.5	Installation depth 19.5	Installation depth 19.5	Installation depth 19.5	Installation depth 20.5 Ignition voltage < 100 V	Installation depth 20.5 Ignition voltage < 100 V						Installation depth 16.2	shortened gate		
Stock version		●	●	●	●	●	●	●		●	●					●	●