

PRODUCT-DETAILS

TY150-18

CABLE TIE 18LB 5IN NATURAL NYL



General Information

Extended Product Type	TY150-18
Product ID	7TAG054360R0149
EAN	5415022141115
Catalog Description	CABLE TIE 18LB 5IN NATURAL NYL
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor or Outdoor Applications, Length of 162mm (6.38 Inches), Width of 2.5mm (0.10 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds)

Ordering

EAN	5415022141115
UPC	786209515063

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	9 in 229 mm
Package Level 1 Height	3.25 in 83 mm
Package Level 1 Depth / Length	12 in 305 mm
Package Level 2 Units	20000 piece
Package Level 2 Width	12.5 in

	318 mm
Package Level 2 Height	12 in
	305 mm
Package Level 2 Depth / Length	18 in
	457 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Catamount
Bundle Diameter	1.5 in 38.1 mm
Color	Natural
Effective Date	20130116
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	PLASTIC CABLE TIE
Product Type	General Purpose
Standards	UL E49405
Tensile Strength	18 lb 80 N
Thickness	0.05 in 1.2 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY150-18
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY150-18

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

|