

NITREX

Nitrex 244 (244*)

10 gauge seamless HPPE liner in blue · cut resistant level D · ambidextrous
food approved · low linting · NitreGuard® Technology

Physical Specifications:

Material: HPPE, Glass,
Polyester
Colour: Blue

Order Codes | Sizing:

244/06 | 6
244/07 | 7
244/08 | 8
244/09 | 9
244/10 | 10
244/11 | 11

Size 06 | XS Size 07 | S Size 08 | M
Size 09 | L Size 10 | XL Size 11 | XXL

Packaging:

1 piece per polybag
50 polybags per case

Classification:



Features

- Featuring Unigloves NitreGuard Technology
- 10 gauge seamless polyester liner with HPPE and encapsulated glass fibre
- Cut resistant level D
- Ambidextrous
- Low linting
- Food approved

Benefits

- Unigloves NitreGuard Technology is awarded to gloves achieving a high-performance in the straight blade cut test
- Seamless polyester liner with HPPE and encapsulated glass fibre is breathable and ideal for use in areas where cut protection is required
- EN ISO cut level D ($\geq 15N$ & $< 22N$) designed to protect against high level cut hazards
- Can be worn on either hand extending the life of the glove
- Low linting to avoid contamination
- Approved for use in food prep and handling

Sectors

- Food



For more about the Nitrex range, please [click on the image](#)



UNIGLOVES UK
Registered in England No: 4010200
VAT registration 791817787

3 Ambley Green, Gillingham Business Park,
Gillingham, ME8 0NJ, UK
+44 (0)800 049 6602
enquiries@unigloves.co.uk
unigloves.co.uk

UNIGLOVES GERMANY
Arzt- & Klinikbedarf
Handelsgesellschaft mbH

Camp-Spich-Straße 71
D-53842 Troisdorf-Spich,
+49 (0) 2241-9323-0
unigloves@unigloves.de
unigloves.de



Neither this document nor any other statement made herein by or on behalf of Unigloves should be interpreted as a guarantee of marketability or that any Unigloves product is fit for a particular purpose. Unigloves accepts no responsibility for the adequacy or suitability of a user's selection of gloves for their intended application.

Issue No. 1

Prepared at Gillingham
on 06/01/22