




Relamp LED T8 Tube Fixture 1x 600 G13 IP20

Article number: 147153

BAI Surface-mounted Batten for LED Tube 1xT8 600mm G13 230V/AC (lamp not included) IP20 CLI 614x41x63mm

Discover the versatility of the Relamp empty T8 fixtures without ballast – the ideal housing for a T8 EM+AC LED tube with a G13 base. This highly compact fixture, featuring a durable steel housing, is easy to install using the included plugs and screws. The LED tube can be fitted effortlessly with a simple twist. Choose the LED tube that best suits your application and benefit from maximum flexibility. Suitable for through-wiring and single-ended power supply. Note: this fixture is designed exclusively for LED tubes and is not compatible with traditional fluorescent tubes. Part of the sustainable Relamp series by Bailey: Relamp – Reduce – Reuse.



General ETIM properties

ETIM group	Luminaire
ETIM class	Batten luminaire
Name	Relamp LED T8 Tube Fixture 1x 600 G13 IP20
Brand	Bailey
Productseries	Relamp T8
Producttype	LED T8 FIXTURE 600

ETIM specifications

Length [mm]	614
Lamp type	LED exchangeable
With light source	No
Suitable for number of light sources	1
Lamp holder	G13
Suitable for lamp power [W]	18 - 18
Material	Steel
Housing colour	White
Voltage type	AC
Nominal voltage [V]	220 - 240
Type of control gear	Not required
With control gear	No
Exchangeable control gear	No
Light distributor	None
Degree of protection (IP)	IP20
Protection class according to IEC 61140	I
Luminaire with limited surface temperature, sign "D" according to EN 60598-2-24	No
Covering of the luminaire with thermally insulating material possible	No
Suitable for emergency lighting	No
Filament test according to IEC 60695-2-11	650 °C - 30 s
With switch	No
With movement sensor	No
Max. system power [W]	18
Colour of light adjustable	No
Luminous flux adjustable	No
Beam angle adjustable	No
Width [mm]	41
Height/depth [mm]	63
Type of wiring	Ending
Number of poles	3
Conductor cross section [mm²]	0.5
Connection type	Screwed terminal
Electrical connection with connector system	Yes
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
With lamp protection basket	No
Operation by Bluetooth	No
Compatible with Casambi	No
Dimmable	No

Dimming DALI-2	No
Containing product according to 2019/2020/EU No	
Impact strength	IK08
Emergency power supply system	None
Emergency function monitoring system	None
With presence detector	No
With light sensor	No
Connectable conductor cross section [mm²]	0.5 - 2.5

Alternative articles



146960

Relamp LED T8 Tube Batten 1x
600 G13 IP65 IK10

Complementary articles



145758

LED Ecobasic T8 600 G13 10W
(18W) 1000lm 865 EM+AC



80100040811

LED Ecobasic T8 600 G13 10W
(18W) 950lm 830 EM+AC