

# rotronic

**Datenblatt - Fiche technique - Data sheet**


**11.01.6590**



**ROLINE Monitor-Anschlusskabel HD15 ST/BU, 10,0m**

**ROLINE Câble pour écran HD15 F – HD15 M A-B, 10,0m**

**ROLINE VGA Cable, HD15 F – HD15 M, B-A, 10 m**




NOTE:

注:线材颜色须用RLA专用米色!

1. CABLE: 28AWG, NON-UL, AL-FOIL, 14C+1, BEIGE COLOR, OD=6.0mm, PVC JACKET.
2. LENGTH: 10M.
3. CONNECTORF: HDB15M \* 1PCS, HDB15F \* 1PCS (黑胶芯)
4. MLOD: 成型APPLE模 — 成型APPLE模
5. SCREW: #4\*40 INCH SCREW \* 4
6. CONTACTS:
 

HDB15M	1	2	3	4	5	6	7	8	10	11	12	13	14	15	64
HDB15F	1	2	3	4	5	6	7	8	10	11	12	13	14	15	64
7. OPEN/SHORT: 100% TEXT.  
INSULATION: 1M.
8. ALL MUST BE ROHS COMPLIANT.



PE BAG(250\*360\*0.06)  
+ 吊卡+条码贴纸包装  
25PCS/CTN

COMPANY	RLA		ITEM NO.	11.01.6590	NO	B	Rotronic Co., Ltd.	SCALE	NON
REVISION	DATE	DISCRIPTION	DRAWN BY					UNIT(mm)	⊕
REV.A/0	2006.12.21	S	DESIGNED BY					DRAWING NO.	
			APPROVAL BY						