



Main

Range	Merten
Product name	Merten inserts
Product or component type	Shutter control
Device presentation	Mechanism with fixing frame

Complementary

Device mounting	Flush
Fixing mode	By screws and claws
Actuator	Rocker
Technology type	Electromechanical
Number of rocker	2
Control type	Switch
Switch function	1-pole
Interlocking type	Electrical and mechanical
[Ue] rated operational voltage	250 V
Network type	AC
Network frequency	50/60 Hz
Rated current	10 AX
IP degree of protection	IP20
Width	71 mm
Height	71 mm

Offer Sustainability

Sustainable offer status	Green Premium product
Cradle to Cradle	Silver
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins