

KERN HBA 100-0

KERN

Compact handheld durometer with drag indicator



Net weight	0,15 kg
Shipping method	Parcel service
Net weight approx.	0,15 kg
Gross weight approx.	0,50 kg
Shipping weight	0,46 kg

Pictograms

STANDARD



Category

Brand	Sauter
Product category	Hardness testing
Product group	Analogue Shore hardness tester
Product family	HB

Measuring System

Measuring range Shore	100
Readability hardness [d] (Shore)	1
Measuring probe diameter	18 mm
Test force Hardness measurement	10 N
Test object thickness [Min]	6 mm
Hardness scales	Shore A
Units	HA
Tolerance (% of [Max])	3%

Construction

Dimension (W×D×H)	115×60×25 mm
Dimension housing (W×D×H)	115×60×25 mm
Material housing	metal
Scale - Display type	Analogue

Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	40 °C

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	147×98×54 mm