

ROHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

07/18/2013

UNITS = inches [mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE: SHEET OF 2 3

DWG NO. 681M17W2103LYYY


REV


5

## ALL CLINCH-NUTS ARE 4-40 INTERNAL THREADS


## **TOLERANCE**:

ALL DIMENSIONS ARE ±0.010







2 .... 0.236" PCB SIDE




4 ..... 0.237" PCB SIDE







3 ..... 0.236" MATING SIDE




5 ..... 0.224" PCB SIDE



6 ..... 0.224" PCB SIDE/JACKSCREW





# Roks Comp



DRAWN: M. SIGMON DATE: 07/18/2013

## UNITS = inches [mm]

#### DO NOT SCALE FROM DRAWING REV SCALE: SHEET OF

*NorComp* 

NTS	3	3	
VG NO.	681M17\	N2103I	YYY

5