



C O M E T
 umetni brusi in nekovine, d.o.o.
 Tovarniška 5, 3214 Zreče, Slovenija
 http://www.comet.si E-mail: comet@comet.si
 Tel.: +386 (0)3 7575 000
 Fax: +386 (0)3 7575 100

ISO 9001
 ISO 14001

BUREAU VERITAS
 Certification

N° 221335 / N° 193494



TECHNICAL SPECIFICATION

No.: Flex 246891.....

PRODUCT :

TYPE	CUT-OFF WHEEL	Code:	PHET12510FI
FORM	F41		
DIMENSION	125x1x22,23		
QUALITY	20A60R-BF		
OPERATING SPEED	80 m/s		
REINFORCEMENT	2A		
LABEL	PHOENIX THIN		

CHARACTERISTICS :

CHARACTERISTICS	VALUE	TOLERANCES	CONTROL METHODS
THICKNESS	1,25 mm	± 0,05 mm	internal method
WEIGHT	32 g	±2g	internal method
FACTOR	2	± 0,5	internal method
DESTRUCTION SPEED	min.21200 min ⁻¹	/	SIST EN 12413
UNBALANCE	max. 1,0g	/	ISO 6103
RUN OUT TOLERANCE	0,6 mm	/	ISO 13942

Issue date:	Author :	Approved by :
06.11.2009	Research technologist: Zlatko Jereb	Production Manager: Milen KRAJNIK, inž.