

POLYSTEEL 1000

PURE BEAM FOCUSING

1000 LUMENS | 351M BEAM | 85H



BATTERY TYPE	9 x AA (Alkaline)
BEAM DISTANCE (HIGH)	1151 ft / 351 m
BEAM DISTANCE (LOW)	357 ft / 109 m
BEAM DISTANCE (MEDIUM)	662 ft / 202 m
INCLUDED	9 x AA Batteries
LENGTH	10.2 in / 25.9 cm
LIGHT OUTPUT (HIGH)	1000 Lumens



CRUSH PROOF

The Crush Proof feature combines a super-tough stainless steel core with a grip-textured poly-nylon exterior to build unimaginable strength into highly functional lights



DROP PROOF

Verified Drop Proof by ANSI FL1 drop testing from 3 meters high for use in rugged, high-impact environments.



HIGH MEDIUM LOW

Control your light power with the push of a button. Cycle between full light, medium light and low light options.



IPX8 RATING

Work or play in a downpour—or even underwater. COAST lights that have passed the IPX8-level waterproof test keep working even after 6 hours at a depth of 3 meters (9.9 feet).



PURE-BEAM FOCUSING OPTIC

Pack two powerful beams into one and seamlessly transition—with no halos or hot spots—between short and long-range viewing. COAST's patented focusing technology adapts to your need. The Ultra View Flood beam delivers edge-to-edge clarity in a broad circle of light up to 11.5 feet / 3.5 meters across, and the Bulls-Eye Spot beam sends a sharp ray of light at a distance of up to 1151 feet / 351 meters, with a transitional halo around the spot to increase the effective viewing area.



TWIST FOCUS

Dial in the shape of light you need for the situation. COAST's Twist Focus system makes it easy to move between spot and flood beams by simply rotating the head of the flashlight.



WATERPROOF

Beam bright even in a downpour. COAST waterproof lights and headlamps keep shining—in full luminescent power—even after being submerged underwater for hours.