

12 Point Laminated Double Box Ratcheting Wrenches

Laminated Double Box Ratcheting Wrenches are available in the most common SAE sizes in flat styles. The open head and body design are easy-to-clean to ensure dirt and debris does not get trapped blocking the ratcheting mechanism. The openings are broached for an accurate, non-slip on fasteners. The wrenches are heat treated for durability and are chrome plated for corrosion resistance. Wrenches are reversible by turning the wrench over.

- Made in the USA
- Easy to Clean Dirt and Debris from Ratcheting Mechanism
- Chrome Plate Resist Rust and Corrosion
- Broached Openings Allow for Non-Slip on Fasteners

Part Number Product Description

27-588G	12 Point Ratcheting Box Wrench 1/4 x 5/16"
27-591G	12 Point Ratcheting Box Wrench 3/8 x 7/16"
27-594G	12 Point Ratcheting Box Wrench 1/2 x 9/16"
27-596G	12 Point Ratcheting Box Wrench 5/8 x 11/16"
27-599G	12 Point Ratcheting Box Wrench 5/8 x 3/4"
27-601G	12 Point Ratcheting Box Wrench 13/16 x 15/16"
27-602G	12 Point Ratcheting Box Wrench 3/4 x 7/8"
27-603G	12 Point Ratcheting Box Wrench 1 x 1-1/16"
27-604G	12 Point Ratcheting Box Wrench 1-1/8 x 1-1/4"