

## FEATURES

- **2 CO Contacts:** Provides flexibility in switching applications
- **16 A Contact Current:** Supports high current loads for robust performance
- **15 Timer Functions:** Offers versatility in timing applications
- **DIN Rail Mount:** Facilitates easy installation and maintenance
- **IP20/IP41 Rating:** Ensures protection against dust and limited ingress of moisture
- **Wide Operating Temperature Range:** Operates effectively from -25 °C to 60 °C
- **Screw Terminal Type:** Ensures secure and reliable connections

## RS PRO 16 A Timer Relay, 2 CO Contacts

RS Stock No: 631-065



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO Timer Relay is designed for precise timing control in industrial applications. With a current rating of 16 A and dual changeover contacts, it ensures reliable operation in automation systems. Its compact design allows for easy integration into DIN rail setups, making it ideal for space-constrained environments.

## General Specifications

Function	Timer Relay
Mount Type	DIN Rail
Number of Contacts	2
Number of Timer Functions	15
Product Type	Timer Relay
Terminal Type	Screw

## Electrical Specifications

Contact Configuration	2 CO
Contact Current	16 A
Supply AC Voltage	190-260 V ac

## Mechanical Specifications

Height	90.2 mm
Length	62.5 mm
Width	36.3 mm

## Protection Category

IP Rating	IP20, IP41
-----------	------------

## Operation Environment Specifications

Maximum Operating Temperature	60 °C
Minimum Operating Temperature	-25 °C

## Approvals

Standards/Approvals

CE, cULus, DEKRA, IEC, IONET, K-Q TSE-ISO-EN 9000, MID