


9980

Max. 24 VA

AC/AC DESKTOP

- Max 24 VA output power
- 230 VAC input voltage
- Available with EU or UK terminals
- Compliance with relevant worldwide safety standards
- Exchangeable output plugs, providing:
 - reduced stocking requirements
 - short delivery lead times
 - snap-locks for added safety



<u>Technical specifications</u>	9 V	12 V	24 V	24 V
<i>Input voltage:</i>	230 VAC, 50 Hz			
<i>Output voltage:</i>	9VAC	12VAC	24VAC	24VAC
<i>Max.output power:</i>	9VA	12VA	12VA	24VA
<i>Max. Load current:</i>	1A	1A	0,5A	1A
<i>Temperature range:</i>	-10°C to +40°C			
<i>Protection:</i>	Thermal fuse in primary			
<i>Insulation class</i>	II			
<i>Electrical safety</i>	EN 60950			
<i>EMC, Emission</i>	EN 61000-6-3			
<i>EMC, Immunity</i>	EN 61000-6-1			
<i>Mains connections:</i>	EU or UK			
<i>Output terminals:</i>	Secondary cable w/snap-on plugs			
<i>Dimensions: EU+UK</i>	81x56x49mm			
<i>Weight: UK</i>	540g	560g	540g	680g
<i>Weight: EU</i>	490g	500g	500g	620g