



ENGLISH

Datasheet

RS Pro Black Ethylene Polypropylene (EPDM) Sheet, 1200mm x 600mm x 6mm

RS Stock No: **840-5535**



Product Details

RS Pro rubber sheet made of ethylene polypropylene (EPDM) in black colour, measures 1200 x 600 mm with a thickness of 6 mm. This rubber sheet offers excellent resistance to weathering and is perfect to use within the temperature range of -40 to 100 deg C.

Features and Benefits

- Water byelaws listed grade
- EPDM rubber may be used in all applications involving cold potable water use
- Excellent resistance to weathering
- Temperature range: -40 to +100°C



ENGLISH

Specifications:

Colour	Black
Suitability	WRAS approved for use with potable water
Density	1.13 g/cm ³
Elongation	328 to 420%
Length	1200 mm
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-40°C
Thickness	6 mm
Width	600 mm
Finish	Plate/Cloth
Hardness	68 to 73 IRHD
Material	EPDM
Standards Met	RoHS Compliant; BS EN 681/1
Tensile Strength	11 to 12.5 MPa