

# PORT-ROLL

## BLUE MANULASTIC WHEEL



**STRONG POINTS**

- Very flexible materials handling
- Low starting effort.
- Non-marking tyre.



### APPLICATIONS

*Flexible and easy materials handling on all types of industrial surfaces, even those in poor condition.*

*Does not leave scratches or other types of mark on surfaces, high degree of resistance to abrasion.*

**CASTOR ASSEMBLY:** • Swivel or fixed. • Pressed steel. • Fastening by top plate. • Swivels on two rows of balls. • Bright zinc-plated protection.

**WHEEL:** • **blue Manulastic:** super-elastic blue rubber tyre bonded onto the black polyamide-6 centre. • Plain bearing or with roller bearing. • Zinc-plated steel threadguards. • Bolted axle.

**LOCKING:** • **MB** • Meta-bloc: double-action rear brake: wheel and swivel. • Steel pedal.

Icon	Icon	Icon	Icon	Icon	Icon	Icon	Icon	Icon	Type	Icon	Code	EAN 13	
<b>80</b>	32	107	42	33	105x80	80x60	9	<b>80</b>			0,750	127 7210	339680 604037 9
											0,950	1 275 7210	339680 604039 3
											0,350	508 7210	339680 604038 6
<b>100</b>	32	127	46	41	105x80	80x60	9	<b>150</b>			0,815	127 7221	339680 604041 6
											0,910	1 270 7221	339680 604043 0
											0,565	508 7221	339680 604045 4
<b>125</b>	32	156	46	45	105x80	80x60	9	<b>150</b>			1,185	216 7222	339680 604046 1
											1,515	2 170 7222	339680 604047 8
											0,795	516 7222	339680 604048 5

**80**  
**150**  
daN