

Heat Gun - HL 1820S



TECHNICAL SPECIFICATIONS	
Dimensions (LxWxH):	252 x 82.5 x 200mm
Power Supply:	110V or 240V
Output:	1300W
Temperature:	50 / 400 / 550°C
Airflow Rate:	100 / 200 / 300 l/mm
Stages:	3
Highlights:	Hanger, high durability (+20%), optimised weight balance.
Power Cord Length:	2,20m
Motor:	Brush Motor
Motor Life:	600 hours
Heating Element:	Micanite Heating Element
Weight:	800g
Dimensions:	252 x 82.5 x 200mm