

PC 2828



Sample image

Order symbol : PC 2828

Product nr : 6530803

Description : Base, PC

EAN : 6418074000460

El. number :

- Finland : 3423739
- Denmark : 8212006739
- Sweden : 2539483

Dimensions :	Height	Width	Depth
mm :	280	280	100
inch :	11.02	11.02	3.94

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035

Ratings :

electrical_insulation :	Totally insulated
UV resistance :	UL 746C
Flammability Rating :	UL 94 5VA
Glow Wire Test (IEC 695-2-1) °C :	960C

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175