

Actuator

45-
2234.11H0.000

Distribution by
Rs-online



<https://rs-online.eao.com/component/45-2234.1...>

Your product:



45-2234.11H0.000 Actuator

FRONT

Front dimension:	Ø 29,5 mm
Front form:	Round
Front bezel colour:	Black
Front bezel material:	Plastic

MOUNTING

Design:	Raised
Mounting cut-out:	Ø 22.3 mm
Mounting type:	Panel mounting

OPERATING-/INDICATION PART

Lens colour:	Green
Lens material:	Plastic
Lens illumination:	Illuminated
Lens shape:	Flush
Lens optics:	transparent
Lens type:	Level with front bezel
Illumination colour:	Green

MECHANICAL CHARACTERISTICS

Switching action:	Maintained
Switching system:	Slow-make switching element

Mechanical lifetime: 500 000 cycles of operation
Operating frequency: Max. 1 800/h
Weight: 0.02 kg

AMBIENT CONDITION

IP front protection: IP66, IP67, IP69K
Operating temperature: – 25 °C ... + 70 °C
Storage temperature: – 40 °C ... + 80 °C
Shock resistance: According to IEC 60068-2-27: Sinusoidal half-wave 50 g / 11 ms
Vibration resistance: According to IEC 60068-2-6: 20 ... 500 Hz: 5 g
Climate resistance: During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6

CERTIFICATE


REACH: REACH compliant
RoHS: RoHS compliant

OTHER

Short Description: Actuator, Ø 22.3 mm, Ø 29,5 mm, Flush, Illuminated, Green, Plastic, transparent, Round, Black, Plastic, Maintained, IP66, IP67, IP69K, Green
Housing colour: Black
Housing material: Plastic
Product attributes: Push to unlatch
Hints: Push to unlatch
Wiring diagrams:



Mounting cut-outs:



Dimension drawings:

