

FEATURES

- **2 m cable length:** Provides ample reach for connecting devices at a distance.
- **Right angle plug:** Facilitates connections in confined spaces, reducing strain on the cable.
- **16 A current rating:** Supports high-power devices, ensuring efficient performance.
- **Polyvinyl Chloride jacket:** Offers durability and protection against environmental factors.
- **White jacket colour:** Enhances visibility and identification in complex setups.

RS PRO 2 m Power Cable, 16 A Right Angle Plug

RS Stock No: 558-941



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO power cable is designed for reliable electrical connections in various industrial and commercial settings. With a 2-metre length and a right angle plug, it offers flexibility and ease of use in tight spaces. The cable is suitable for applications requiring a 16 A current rating and supports up to 250 V, making it ideal for powering a range of electrical devices.

General Specifications

Connector Type B	CEE 7
Jacket Colour	White
Product Type	Power Cable

Mechanical Specifications

Cable Length	2 m
Jacket Material	Polyvinyl Chloride

Electrical Specifications

Current Rating	16 A
Mains Plug Type	Right Angle Plug
Voltage	250 V

Approvals

Standards/Approvals	CEBEC, D, EAC, FI, ICC, IMQ, KEMA, KEUR, N, NF, OVE, S, VDA
---------------------	---

