

# NBK

333 Pfingsten Road  
Northbrook, Illinois 60062-2096  
(708) 272-8800  
FAX No. (708) 272-8129  
MCI Mail No. 254-3343  
Telex No. 6502543343



Underwriters Laboratories Inc. ®

File E81856

Vol 1

Issued 07/15/86

Revised 06/14/94



## FOLLOW-UP SERVICE PROCEDURE (TYPE R)

COMPONENT - MOTOR CONTROLLERS, MAGNETIC  
(NLDX2, NLDX8)

Manufacturer: SEE ADDENDUM FOR MANUFACTURING LOCATIONS

Applicant: FINDER S P A  
(702536-001) VIA DRUBIAGLIO 14  
I-10040 ALMESE (TO) ITALY

Recognized Company: SAME AS APPLICANT  
(702536-001)

This Procedure authorizes the above Manufacturer to use the Recognized Marking of Underwriters Laboratories Inc. only on Recognized products covered by this Procedure, in accordance with the Recognition and Follow-Up Service Agreement.

The prescribed Mark or Marking shall be used only at the above manufacturing location on such products which comply with this Procedure and any other applicable requirements.

The Procedure contains information for the use of the above named Manufacturer and representatives of Underwriters Laboratories Inc. and is not to be used for any other purpose. It is lent to the Manufacturer with the understanding that it is not to be copied, either wholly or in part, and that it will be returned to Underwriters Laboratories Inc. upon request.

This PROCEDURE, and any subsequent revisions, is the property of UNDERWRITERS LABORATORIES INC. and is not transferable.

UNDERWRITERS LABORATORIES INC.

*Robert H. Levine*

Vice President, Follow-Up Services

COVERAGE BASED ON CANADIAN STANDARDS:

The products tabulated below also comply with the requirements of CSA Standard for Industrial Control Equipment, C22.2 No. 14-M91.

Marking Requirements - These products are intended to be marketed in Canada. Markings shall be based on the "Marking" provisions of the Section General and each individual section within this volume.

The necessity for a bilingual marking (i.e., English and French) shall be determined by the Listee, depending upon which Provinces in Canada the product will be marketed. When the product identification is also required in French, the French translation shall be consistent with the English version as described in each individual section. The above CSA Standard presently only requires bilingual marking of warning and cautionary statements when applicable. Unless specified otherwise, the products are not required to be marked with any warning or cautionary statements.

<u>Model/Type</u>	<u>Type of Product</u>	<u>Section</u>
* All	Industrial control equipment	All

D E S C R I P T I O NPRODUCT COVERED:

Series 60, followed by 1, 3, 4 or 6, followed by 2 or 3, followed by 8 or 9, may be followed by 6, 12, 24, 48, 110, 230 or 240, followed by 0, may be followed by 00, 01, 02, 03 or 04, may be followed by 0 with Suffix U. Special Nos. 6531, 6531-03, 65.61 and 65.61.03. Relay Receptacles, Part Nos. 90.12, 90.13, 90.22, 90.23, 90.31, 90.32.

GENERAL:

These devices are open magnetically operated plug-in relays and sockets. They are intended to be used in industrial control equipment applications for the suitability of the combination has been determined by Underwriters Laboratories Inc.

Ratings - They are rated:

Contact Ratings: Series 60 - 10 A (resistive), 250 V ac; standard duty pilot duty, 120/240 V ac; 10 A general purpose), 240 V ac maximum.

Nos. 6531 and 65.61 - (same polarity) - Same as Series 6531-03 except no direct current ratings.

Nos. 6531-03 and 65.61.03 - (same polarity) - 20 A (resistive), 277 V ac; standard duty pilot duty, 125/250 V dc; 20 A (general purpose), 277 V ac maximum.

\* Coil Ratings: 6, 12, 24, 48, 110, 120-220, 230 or 240 V ac; 6, 12, 24, 48, 60-125 or 110 V dc.