

Datasheet

**RS Pro 3 → 20 V dc 86dB sound Through Hole
Continuous Internal Piezo Buzzer, 2900 → 3900 Hz**
RS Stock No: **754-1996**



Product Details

RS Pro internal piezo buzzer operates at a voltage range of 3 - 20 V dc. This continuous buzzer delivers 86 dB sound at a frequency range of 2900 - 3900 Hz. It is suitable for applications that require high sound output.

Features and Benefits

- Circular cased PCB mounting
- High sound output buzzers
- Continuous delivery

**Specifications:**

Drive Type	Internal
Mounting Type	Through Hole
Tone Type	Continuous
Diameter	24.5 mm
Dimensions	24.5 (dia.) x 16 mm
Height	16 mm
Maximum Frequency	3900 Hz
Maximum Operating Temperature	+85°C
Maximum Supply Voltage	20 V dc
Minimum Frequency	2900 Hz
Minimum Operating Temperature	-30°C
Minimum Supply Voltage	3 V dc
Sound Level	86 dB
Supply Current	9 mA