

910.11 SS G1/2B / G1/2 LH-RH union DIN 16272

DIN-Shut-off valve

Item number: 9091017

Quantity: 1 pcs.

Order code: 910.11-SS31BA-1ZZ-P32-ZZ 0

Overview: 910.11 SS G1/2B / G1/2 LH-RH union DIN 16272

DIN-Shut-off valve

Material body: Stainless steel 1.4571

Version: with separate isolating test connection, per DIN 16272

Connection process side + instrument side: G 1/2 B male + G 1/2 LH-RH union

Design: Form A, with LH-RH union

Test connection: M20 x 1,5

Material packing: PTFE

Permissible medium temperature: -40...+200°C

Nominal pressure: PN max. 400 bar

Details:

DIN-Shut-off valve

Specifications according to data sheet: AC 09.02

Version: with separate isolating test connection, per DIN 16272

Material body: Stainless steel 1.4571

Material packing: PTFE

Permissible medium temperature: -40...+200°C

Nominal pressure: PN max. 400 bar

Design: Form A, with LH-RH union

Connection process side + instrument side: G 1/2 B male + G 1/2 LH-RH union

Test connection: M20 x 1,5