




## TransMemory U401

<b>Retail Part Number</b>	<b>Global</b>	LU401S016GG4	LU401S032GG4	LU401S064GG4
	<b>China</b>	LU401S016GC4	LU401S032GC4	LU401S064GC4
<b>Brand name</b>		TransMemory™	TransMemory™	TransMemory™
<b>Product</b>		USB Flash Drive	USB Flash Drive	USB Flash Drive
<b>Interface</b>		USB 2.0	USB 2.0	USB 2.0
<b>Capacity</b>		16GB	32GB	64GB
<b>Product Color</b>		Silver	Silver	Silver
<b>Country of origin</b>		Taiwan	Taiwan	Taiwan
<b>Bulk Picture</b>				
<b>Pre Format Type</b>		FAT32	FAT32	FAT32
<b>Approximate Usable Capacity *1</b>		14.4GB	28.8GB	57.6GB
<b>Supported SuperSpeed</b>		-	-	-
<b>Supported high-speed</b>		0	0	0
<b>Supported Full Speed</b>		0	0	0
<b>Max. Read Speed (SuperSpeed) *2</b>		-	-	-
<b>Max. Write Speed (SuperSpeed) *2</b>		-	-	-
<b>Max. Read Speed (high-speed) *2</b>		-	-	-
<b>Max. Write Speed (high-speed) *2</b>		-	-	-
<b>Supported OS Windows 10</b>		0	0	0
<b>Supported OS Windows 8.1</b>		0	0	0
<b>Supported OS X</b>		OS X v10.11, macOS v10.12 - v10.15	OS X v10.11, macOS v10.12 - v10.15	OS X v10.11, macOS v10.12 - v10.15
<b>Bulk Dimensions</b>	<b>mm(Approx.)</b>	L:38.0, W:12.2, H:4.5	L:38.0, W:12.2, H:4.5	L:38.0, W:12.2, H:4.5
<b>Bulk Weight(Approx.)</b>		6g	6g	6g
<b>Ambient Operating Temperature Range *3 (without condensation)</b>		0 to 50°C	0 to 50°C	0 to 50°C
<b>Enclosure of an adapter</b>		-	-	-
<b>RoHS Compliance</b>		V	V	V
<b>Package Type</b>	<b>Global China</b>	Blister	Blister	Blister
<b>Package Dimensions(mm)</b>		W:76,D:127,H:6	W:76,D:127,H:6	W:76,D:127,H:6
<b>Package Weight(Approx.)</b>		13.3g (Typ)	13.3g (Typ)	13.3g (Typ)
<b>Carton Quantity (Units per box)</b>		20 units per inner carton; 20 inner cartons per outer carton (400 units per outer carton)	20 units per inner carton; 20 inner cartons per outer carton (400 units per outer carton)	20 units per inner carton; 20 inner cartons per outer carton (400 units per outer carton)
<b>Inner Carton Dimensions(mm)</b>		W: 129,D: 82,H: 78	W: 129,D: 82,H: 78	W: 129,D: 82,H: 78
<b>Inner Carton Weight(Approx.)</b>		290g (Typ)	290g (Typ)	290g (Typ)
<b>Outer Carton Dimensions(mm)</b>		W: 272,D: 425,H: 182	W: 272,D: 425,H: 182	W: 272,D: 425,H: 182
<b>Outer Carton Weight(Approx.)</b>		6320g (Typ)	6320g (Typ)	6320g (Typ)
<b>Units per Pallet</b>		Approx. 11200 units per pallet	Approx. 11200 units per pallet	Approx. 11200 units per pallet
<b>Layers per Pallet</b>		Approx. 7	Approx. 7	Approx. 7
<b>Quantity per Layer</b>		Approx. 1600 units	Approx. 1600 units	Approx. 1600 units

\*1: This product is labeled based on the flash memory it contains, not the actual memory capacity available for data storage. Part of the capacity is reserved for card functionality.

(For purposes of measuring memory capacity in this context, 1GB = 1,073,741,824 bytes)

\*2: 1 MB/s is calculated as 1,000,000 bytes/s. The value is the best value obtained in specific test environment at KIOXIA Corporation and KIOXIA Corporation does not warrant read speed use in individual devices. Read speed may vary depending on user-specifications such as devices used and file size read.

\*3: Based on KIOXIA Corporation's test results. The operation in all the situations is not warranted. KIOXIA Corporation does not warrant any data stored on the product.

● macOS, OS X are trademarks of Apple Inc.

● All other company names, product names, and service names mentioned herein may be trademarks of their respective companies.

● Product specifications and design are subject to change without prior notice.